

# Q2A404N

by Burndy  
Catalog ID: Q2A404N

Prop 65 Notice

Copper Terminal, 4 Hole, 600-800 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws



## Product Details

### General

Connector Type	Terminal
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810322529
UPC 12 Digit	7818103225299

### Dimensions

Dimension - B Length inch	4.49 in
Dimension - D inch	3.12 in
Dimension - F Width Center to Center inch	2.00 in
Dimension - Height fraction	2-7/16 in
Dimension - Height inch	2.56 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Stud Size inch	1/2
Dimension - Width fraction	4-11/32 in
Dimension - Width inch	4.34 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - Copper Str Size	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	600 kcmil-800 kcmil
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	2
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)