

## Q3A444N

by Burndy  
Catalog ID: Q3A444N

Prop 65 Notice

Copper Terminal, 4 Hole, 850-1000 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 3 Screws



## Product Details

### General

Connector Type	Terminal
Installation Torque Recommended Run in-lb	500 in-lb
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810323885
UPC 12 Digit	7818103238855

### Dimensions

Dimension - D inch	3.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2-3/4
Dimension - Height inch	2.56 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.19 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.25 in
Dimension - Stud Size inch	1/2
Dimension - Width fraction	6-5/8 in
Dimension - Width inch	5.88 in
Dimension - Width mm	149 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor - Copper Str Size	850 Kcmil;1000 Kcmil
Conductor - Copper Str Size Range	850 Kcmil-1000 Kcmil
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)