

Q3A464N

by Burndy
Catalog ID: Q3A464N

Prop 65 Notice

Copper Terminal, 4 Hole, 1100-1500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 3 Screws



Product Details

General

Connector Type	Terminal
Installation Torque Recommended Run in-lb	600 in-lb
Installation Torque Recommended in-lb	600 LBS/in
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006016
UPC 12 Digit	7818100060166

Dimensions

Dimension - D inch	3.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	3-1/8
Dimension - Height inch	2.94 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.50 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.50 in
Dimension - Stud Size inch	1/2
Dimension - Width fraction	7-7/8 in
Dimension - Width inch	6.81 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	1100 Kcmil;1500 Kcmil
Conductor - Copper Str Size Range	1100 Kcmil-1500 Kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)