



QA262NTN

by Burndy
Catalog ID: QA262NTN

Prop 65 Notice

Heavy Duty, Compact, Cu Mechanical Terminal For Joining a Wide Range of Cable to Equipment Pads, 2/0 - 1/0 Str., 2 Pad Holes, Tin Plated

Product Details

General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810463994
UPC 12 Digit	7818104639944

Dimensions

Dimension - B Length fraction	47/50 in
Dimension - B Length inch	0.94 in
Dimension - Cross Flats inch	0.69 in
Dimension - D inch	3.12 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-4/25 in
Dimension - Height inch	1.16 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.19 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.00 in
Dimension - Width inch	0.81 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)