



QA8CB

by Burndy
Catalog ID: QA8CB

Prop 65 Notice

Copper Terminal, Heavy Duty, 1 Hole, 14 AWG (Sol)-8 AWG (Str), #10 Stud, 1 Screw.

Features: Type QA Heavy Duty, Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Fast One Wrench Installation, Dimension D: 9/16 IN, Dimension T: 5/32 IN, Stud/bolt Hole Size: #10, Number Of Clamping Elements: 1, Dimension K: 7/32 IN, Dimension N: 9/32 IN, Conductor Type: Run: Commercial Stranded Copper, Navy Copper, Tongue Width: 9/16 IN, Length: 1-3/8 IN, Height: 11/16 IN, Installation Torque: 75 IN-LB

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bars
Connector Type	Terminal
Installation Torque Recommended in-lb	75 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810313480

Dimensions

Dimension - D inch	0.56 in
Dimension - Height fraction	11/16
Dimension - Height inch	0.69 in
Dimension - Hole Size fraction	7/32
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - N inch	0.28 in
Dimension - Pad Width inch	0.56 in
Dimension - Stud Size inch	#10
Dimension - Width mm	14 mm
Weight	0.08 lb

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Solid Size Range	14 AWG-8 AWG
Conductor - Copper Str Navy Size	4 (1) Navy;4 (7) Navy;4 (19) Navy;4 (41) Navy;6 (7) Navy;6 (19) Navy;9 (7) Navy;9 (37) Navy;14 (7) Navy;14 (140) Navy
Conductor - Copper Str Navy Size Range	4 (1) Navy-14 (140) Navy
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	14 AWG-8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)