



QB342N

by Burndy
Catalog ID: QB342N

Prop 65 Notice

Cast Cu Alloy Terminal, 2 Pad Holes, 400 kcmil - 500 kcmil, 4.69 IN L, 1.38 IN W, 5/8-18 IN Bolt

Product Details

General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006054

Dimensions

Dimension - B Length fraction	1-19/50 in
Dimension - B Length inch	1.38 in
Dimension - D inch	3.25 in
Dimension - Height fraction	49
Dimension - Height inch	1.94
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.69
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.38 in

Conductor Related

Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)