

QA482N

by Burndy
Catalog ID: QA482N

Prop 65 Notice

High Cu Alloy Terminal, Heavy Duty, 2-NEMA Holes, 1600 - 2000 kcmil
Commercial, 1600 - 2000 Navy, 1 Screw, 0.56" Hole Dia



Product Details

General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810318249

Dimensions

Dimension - D inch	3.00 in
Dimension - Height inch	3.19 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.62 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	2.50 in
Dimension - Width mm	64 mm
Weight	4.3 lb

Conductor Related

Conductor - Copper Str Navy Size	1600 (127) Navy;2000 (127) Navy
Conductor - Copper Str Navy Size Range	1600 (127) Navy-2000 (127) Navy
Conductor - Copper Str Size	1600 kcmil;2000 kcmil
Conductor - Copper Str Size Range	1600 kcmil-2000 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)