



QPX2C2C

by Burndy
Catalog ID: QPX2C2C

Prop 65 Notice

Parallel Clamp, Copper: 6-2 AWG (Run)/ 6-2 AWG (Tap).

Features: The VERSITAP Type QPX Is Recommended For Tee, Cross, Parallel, Butt And Tap Connections, Range-Taking, Only 10 Connectors Required To Accommodate Conductor Sizes From #6 Stranded To 1000 KCMIL, Edges Are Rounded For Easy Taping, Made Of High Strength, High Conductivity Copper Alloy And Silicone Bronze DURIUM Hardware, Conductor Type: Run And Tap: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Stud/bolt Size: 5/16 IN, Length: 1-3/8 IN, Installation Torque: 150 IN-LB, Width: 1-3/8 IN, Height: 1-5/8 IN

Product Details

General

Application	For Tee, Cross, Parallel, Butt And Tap Connections, Copper, Copperweld And Copperweld-Copper
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810341506
UPC 12 Digit	7818103415066

Dimensions

Dimension - B Length fraction	1/3 in
Dimension - B Length inch	0.31 in
Dimension - Height fraction	1-1/2
Dimension - Height inch	1.5
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.38
Dimension - Width mm	35 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - CopperWeld Solid Run	5 AWG
Conductor - CopperWeld Solid Run Range	5 AWG
Conductor - CopperWeld Solid Tap	5 AWG
Conductor - CopperWeld Solid Tap Range	5 AWG
Conductor - CopperWeld Str Run	8 A AWG;8 C AWG;8 D AWG;7 A AWG;7 D AWG;6 A AWG;6 C AWG;6 D AWG;5 A AWG;5 D AWG;5 P AWG;4 A AWG
Conductor - CopperWeld Str Run Range	8 A AWG-4 A AWG
Conductor - CopperWeld Str Tap	8 A AWG;8 C AWG;8 D AWG;7 A AWG;7 D AWG;6 A AWG;6 C AWG;6 D AWG;5 A AWG;5 D AWG;5 P AWG;4 A AWG
Conductor - CopperWeld Str Tap Range	8 A AWG-4 A AWG
Conductor - Nominal Diameter	0.179, 0.182, 0.184, 0.199, 0.206, 0.219, 0.223, 0.225, 0.230, 0.232, 0.246, 0.258, 0.260, 0.276, 0.290, 0.310, 0.320, 0.326
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU Weld C Str-Run • CU Weld C Solid-Run • CU C Str-Tap • CU Weld C Str-Tap • CU Weld C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)