



QB31

by Burndy
Catalog ID: QB31

Prop 65 Notice

Cu Alloy Side Entrance Terminal, 250 - 350 kcmil, 1 Pad Hole

Product Details

General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810116586

Dimensions

Dimension - B Length fraction	1-15/79 in
Dimension - B Length inch	1.19 in
Dimension - D inch	1.56 in
Dimension - Height fraction	1-11/16
Dimension - Height inch	1.69 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.81 in
Dimension - N inch	0.69 in
Dimension - Pad Width inch	1.19 in
Dimension - Width fraction	1-3/16
Dimension - Width mm	30 mm
Weight	0.53 lb

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)