

QQA31

by Burndy
Catalog ID: QQA31

Prop 65 Notice

Terminal, 1 Pad Hole, 250 - 300 kcmil, 250 - 350 Navy, 4-1/8 IN L



Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	325 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006009

Dimensions

Dimension - D inch	1.38 in
Dimension - Height fraction	1.6896551724137931 in
Dimension - Height inch	1.69 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	105 mm
Dimension - Length Overall inch	4.13 in
Dimension - N inch	0.69 in
Dimension - Pad Width inch	1.19 in

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy;300 (91) Navy;350 (91) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy-350 (91) Navy
Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	32
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)