



QPX342C

by Burndy
Catalog ID: QPX342C

Prop 65 Notice

Parallel Clamp, Copper: 250-500 kcmil (Run)/ 6-2 AWG (Tap).

Features: The Versitap Type QPX Is Recommended For Tee, Cross, Parallel, Butt And Tap Connections, Range-Taking, Only 10 Connectors Required To Accommodate Conductor Sizes From #6 AWG Stranded To 1000 KCMIL, Edges Are Rounded For Easy Taping, Made Of High Strength, High-Conductivity Copper Alloy And Silicon Bronze DURIMUM Hardware, Number Of Bolts: 2, Installation Torque: 300 IN-LB, Conductor Type: Run: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Tap: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Length: 1-3/8 IN, Height: 2-3/8 IN, Width: 1-7/8 IN

Product Details

General

Application	For Tee, Cross, Parallel, Butt And Tap Connections
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Material - Hardware	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810343005
UPC 12 Digit	7818103430055

Dimensions

Dimension - Height fraction	2-3/8
Dimension - Height inch	2.38
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88
Dimension - Width mm	48 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG

Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - CopperWeld Solid Run	9 AWG;8 AWG;7 AWG;6 AWG
Conductor - CopperWeld Solid Run Range	9 AWG-6 AWG
Conductor - CopperWeld Solid Tap	5 AWG
Conductor - CopperWeld Solid Tap Range	5 AWG
Conductor - CopperWeld Str Run	4/0 EK AWG
Conductor - CopperWeld Str Run Range	4/0 EK AWG
Conductor - CopperWeld Str Tap	8 A AWG;8 C AWG;8 D AWG;7 A AWG;7 D AWG;6 A AWG;6 C AWG;6 D AWG;5 A AWG;5 D AWG;5 P AWG;4 A AWG
Conductor - CopperWeld Str Tap Range	8 A AWG-4 A AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU Weld C Str-Run • CU Weld C Solid-Run • CU C Str-Tap • CU Weld C Str-Tap • CU Weld C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)