



## QPX4434

by Burndy  
Catalog ID: QPX4434

Prop 65 Notice

Parallel Clamp, Copper: 500-1000 kcmil (Run)/ 250-500 kcmil (Tap).

Features: The Versitap Type QPX Is Recommended For Tee, Cross, Parallel, Butt And Tap Connections, Range-Taking, Only 10 Connectors Required To Accommodate Conductor Sizes From #6 AWG Stranded To 1000 KCMIL, Edges Are Rounded For Easy Taping, Made Of High Strength, High-Conductivity Copper Alloy And Silicon Bronze DURIMUM Hardware, Number Of Bolts: 4, Conductor Type: Run: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Tap: Copperweld - Copper, Copperweld, Commercial Stranded Copper, Installation Torque: 300 IN-LB, Length: 2-1/16 IN, Width: 2-7/16 IN, Height: 3-1/16 IN

## Product Details

### General

Application	For Tee, Cross, Parallel, Butt And Tap Connections
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810345504
UPC 12 Digit	7818103455044

### Dimensions

Dimension - Height fraction	3-1/16
Dimension - Height inch	3.06
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - Width fraction	2-7/16 in
Dimension - Width inch	2.44
Dimension - Width mm	62 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil

Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil
Conductor - CopperWeld Solid Run	6 AWG
Conductor - CopperWeld Solid Run Range	6 AWG
Conductor - CopperWeld Solid Tap	9 AWG;8 AWG;7 AWG;6 AWG
Conductor - CopperWeld Solid Tap Range	9 AWG-6 AWG
Conductor - Nominal Diameter	0.114, 0.128, 0.144, 0.162, 0.600, 0.630, 0.681, 0.728, 0.772, 0.813, 0.893, 0.893, 0.964, 0.998, 1.031, 1.031, 1.094, 1.151
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)