

QQA4C2

by Burndy
Catalog ID: QQA4C2

Prop 65 Notice

Terminal, 2 Pad Hole, #6-4 AWG, 23 - 40 Navy, 2-15/16 in L



Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	110 LBS/in
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810006108

Dimensions

Dimension - D inch	1.19 in
Dimension - F Width Center to Center inch	0.63 in
Dimension - Height fraction	3/4 in
Dimension - Height inch	0.75 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.94 in
Dimension - N inch	0.31 in
Dimension - Pad Width inch	0.63 in

Conductor Related

Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	6 AWG-4 AWG
Conductor - Copper Str Navy Size	23 (7) Navy;30 (19) Navy;40 (19) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	6 AWG-4 AWG

Conductor Type	• CU C Str-Size • CU C Str Navy-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)