



VVA462

by Burndy
Catalog ID: VVA462

V Style Connectors

Product Details

General

Application	Substation
Clamping Element Design	V Bolt
Connector Type	Terminal
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	2.25 x 3.50 - 2 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Trade Name	VARILUG™
Type	Bolted Lugs & Terminals
UPC	621945252288
UPC 12 Digit	6219452522888

Dimensions

Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	1.38 in
Dimension - Height inch	4.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	211 mm
Dimension - Length Overall inch	8.31 in
Dimension - N inch	0.62 in
Dimension - Pad Size inch	2.25 x 3.50
Dimension - Pad Width inch	2.25 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Str Size	1000 kcmil;1250 kcmil;1300 kcmil;1500 kcmil
Conductor - Copper Str Size Range	1000 kcmil-1500 kcmil
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)