

UHR133

by Burndy
Catalog ID: UHR133

Prop 65 Notice

Cast Cu Alloy Bus Support, CU Str. Size: 6 AWG - 500 Kcmil, CU Pipe Size: 1/8"-1/2" IPS, 3 IN Bolt Circle Dia



Product Details

General

Application	Substation
Connector Type	Bus Support
Fitting Type	Rigid Conduit
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque Recommended in-lb	240 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	1/2 X 1" Hot Dipped Galv. Steel Hex. Head Bolts
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810004579
UPC 12 Digit	7818100045799

Dimensions

Bolt Circle Diameter	3.00 in
Dimension - B Length fraction	3-5/8 in
Dimension - B Length inch	3.56 in
Dimension - G inch	1.75 in
Dimension - Height fraction	3 in
Dimension - Height inch	3.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	6 AWG-500 kcmil
Conductor - Copper Tube Std Size	1/8 IPS;1/4 IPS;3/8 IPS;1/2 IPS
Conductor - Copper Tube Std Size Range	1/8 IPS-1/2 IPS
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)