

YA12ATN



by Burndy
Catalog ID: YA12ATN

Prop 65 Notice

UNINSULATED ALUMINUM COMPRESSION TERMINAL, 1-HOLE
DESIGNAL Listed 90° C600 Volts to 35 KV.

Product Details

General

Connector Type	Terminal
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810742754
UPC 12 Digit	7818107427544

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - D inch	0.50 in
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.19 in
Dimension - N inch	0.20 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	#10
Dimension - Z inch	0.30 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	12 AWG
Conductor - AL Str Size Range	12 AWG
Conductor - Copper Str Size	12 Str.
Conductor - Copper Str Size Range	12 Str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL468A-468B
Standards - Industry Standards Met	UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)