

YA252L

by Burndy
Catalog ID: YA252L

Prop 65 Notice

Copper Compression lug, 2 Hole w/ Inspection Window, 1/0 AWG, 5/16" Stud, 7/8" Stud Hole Spacing, Short Barrel, Tin Plated



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810502259

Dimensions

Bolt Size	5/16 in
Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	1.58 in
Dimension - Hole Size mm	8 mm
Dimension - Inside Diameter inch	0.39 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.85 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.36 in
Length	2.85 in

Outside Diameter	0.51 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)