

YA26L245

by Burndy
Catalog ID: YA26L245

Prop 65 Notice

Cu Comp Terminal Code Cond,1 Hole/W/InspWindow, 2/0 AWG Str Code, 125 Navy, 600 V-35 kV, 1/4" Stud, Black, 13 Index



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018651

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.58 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.78 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)