



YA39A13

by Burndy
Catalog ID: YA39A13

Prop 65 Notice

Uninsulated Al Compression Terminal, 2 Holes, 700 - 750 kcmil Al/Cu, 900 kcmil, 600 kcmil CCA DLO(925/22) Al, 600V - 35kV, 1/2" Stud.

UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: Straight

Product Details

General

Application	For Aluminum & Copper Conductors
Color Code	Yellow
Connector Type	Terminal
Die Index	936
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A
UPC	781810438565
UPC 12 Digit	7818104385655

Dimensions

Dimension - B Length fraction	2-7/16 in
Dimension - B Length inch	2.46 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.15 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.07 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.05 in
Dimension - Thread Size	1/2

Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	700 kcmil-750 kcmil
Conductor - Copper Str Size	700 kcmil;750 kcmil
Conductor - Copper Str Size Range	700 kcmil-750 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)