

# YA32LNT12FXG1

by Burndy  
Catalog ID: YA32LNT12FXG1

Prop 65 Notice

Cu Tubing Comp Terminal Flex Cond, Narrow Tongue, 1 Hole/W/InspWindow, 313.1 kcmil Flex, 313.1(775/#24)DLO, 600 V-35 kV, 1/2" Stud, Std bbl, Red, 18/324 Index



## Product Details

### General

Color Code	Red
Connector Type	Terminal
Die Index	18;324
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Narrow
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810374047
UPC 12 Digit	7818103740477

### Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	74 mm

Dimension - Length Overall inch	2.93 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/4
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	313.1 (775/#24)
Conductor - Copper Flex G Size	313.1
Conductor - Copper Flex H Size	313.1
Conductor - Copper Flex I Size	313.1
Conductor - Copper Flex K Size	313.1
Conductor - Copper Flex M Size	313.1
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)