

YA34NT12FXB

by Burndy
Catalog ID: YA34NT12FXB

1 Hole HYLUG Cu Compression Terminal, Belled End, 350 kcmil Flex, 373.7 (925/24) (DLO), 1/2" stud, 4.54" L



Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	19
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810465677

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.48 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.28 in
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.54 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.33 in
Dimension - Strip Length inch	2-9/16
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	373.7 (925/#24)
Conductor - Copper DLO Size Range	373.7 (925/#24)
Conductor - Copper Flex G Size	373.7
Conductor - Copper Flex G Size Range	373.7
Conductor - Copper Flex H Size	373.7
Conductor - Copper Flex H Size Range	373.7
Conductor - Copper Flex I Size	373.7
Conductor - Copper Flex I Size Range	373.7
Conductor - Copper Flex K Size	373.7
Conductor - Copper Flex K Size Range	373.7
Conductor - Copper Flex M Size	373.7
Conductor - Copper Flex M Size Range	373.7

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)