



YA8CL2TC14E190

by Burndy
Catalog ID: YA8CL2TC14E190

Prop 65 Notice

COPPER COMPRESSION TERMINAL.

Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810019252
UPC 12 Digit	7818100192522

Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	1.65 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	47 mm
Dimension - Length Overall inch	1.87 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.34 in

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	8 (37/#24) DLO
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex K Size	8 AWG
Conductor - Copper Flex M Size	8 AWG
Conductor - Copper Flex M Size Range	8 AWG
Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor - CopperWeld C Solid Size	8 AWG
Conductor - CopperWeld Solid Size Range	8 AWG
Conductor - CopperWeld Str Size	8 A AWG;8 C AWG;8 D AWG
Conductor - CopperWeld Str Size Range	8 A AWG-8 D AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)