



YAE14Z2

by Burndy
Catalog ID: YAE14Z2

Prop 65 Notice

Copper Lug, Fork Tongue, w/ Inspection Hole, 16-14 AWG, #4-#6 Stud, Insulated, Short Barrel, Electro-Tin Plated, 600 Volts Max.

Features: INSULUG Type YAE-Z Is Identical To Type YAE-N And Employs A Flanged Fork Tongue For Faster Installation While Maintaining Security If Supporting Screw Becomes Loose, 300 V Maximum, 105 DEG C Max, Flanged Fork: Permits Rapid, Easy Installation Of The Terminal Under The Screw Head Without Complete Removal Of The Screw, Additionally, It May Not Be Removed With Only A Slight Loosening Of The Screw, Package: Bulk, Installation Tool: MR8-33T-1, M8ND Tool With One Of The Following Dies: N14HET-25V1, N10ET-9, N14HET-15, N10ET-23, Y10D, Y10-22 Tool, Insulation Diameter (maximum): 0.156 IN, Tape Mounted Catalog Number: YAE14Z2M, Wire Insulation Grip: Yes, Color Code: Blue, Temperature Rating: 105 DEG C Maximum, Finish: Electro-Tin Plated

Product Details

General

Application	For Faster Installation While Maintaining Security If Supporting Screw Becomes Loose
Color Code	Blue
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Electro Tin
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	YAE-Z, Flanged
UPC	781810804100
UPC 12 Digit	7818108041000

Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.146 in
Dimension - Length Overall inch	0.90 in

Dimension - N inch	0.15 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.25 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL486 Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> UL486 Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)