

YAK31A2G2

by Burndy
Catalog ID: YAK31A2G2

Prop 65 Notice

Cast Al Straight Stacking Lug, 2-NEMA Holes, 350 kcmil, 0.56" Hole Dia



Product Details

General

| | |
|--------------------------------------|----------------|
| Connector Type | Terminal |
| Die Index | 299;705 |
| Feature - Barrel Style | Chamfered |
| Material | Aluminum Alloy |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Trade Name | HYLUG™ |
| UPC | 781810187050 |
| UPC 12 Digit | 7818101870500 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 1.91 in |
| Dimension - Bolt Hole Size inch | 0.50 in |
| Dimension - D inch | 3.25 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - L Length Overall mm | 174 mm |
| Dimension - Length Overall inch | 6.84 in |
| Dimension - N inch | 0.62 in |
| Dimension - Outside Diameter inch | 1.11 in |
| Dimension - P inch | 3.01 in |
| Dimension - Pad Width inch | 1.62 in |
| Dimension - Strip Length inch | 2 in |
| Dimension - Z inch | 0.62 in |
| Physical Attribute - Tongue Angle | Straight |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - AL Str Size | 350 kcmil |
| Conductor - AL Str Size Range | 350 kcmil |
| Conductor - Copper Str Size | 350 kcmil |
| Conductor - Copper Str Size Range | 350 kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 4 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)