



YAV1CL3

by Burndy
Catalog ID: YAV1CL3

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Hole, AN-1 Flex, 1/2" Stud, Short Barrel, Tin Plated.

Features: HYLUG Type YAV Is A Seamless, Heavy Duty Uninsulated Compression Terminal Manufactured From Electrolytic Copper And Is For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, The Seamless Tubing Produces A Double Thick Tongue And Seamless Barrel Design Provides A Strong Connector For Demanding Applications Requiring High Reliability, Applications Include Aircraft, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance, The YAV HYLUG Terminals Meet The Requirements Of SAE-AS7928 And Are Listed Per AS20659 For Use With Copper Aircraft Cable Per MIL-W-5086, The Benefits Of YAV-L Connectors Are The Same As YAV Connectors For Stranded Conductors, Package: Bulk, Installation Tool: HYTOOL: Non-Ratchet: MY28, MY29-11 Tool, MS20659 Dash Number: -134, Finish: Electro-Tin Plated, Wire Shroud: No, Tools, Die Nest Catalog Number, Die Indenter Catalog Number: HYPRESS: Y29NC, Y29B Tool, DV1L Die Nest, Y29PL Die Indenter, (1) Crimp, Y35, Y39 Tool, UV1L Die Nest, Y35P3 Die Indenter, (1) Crimp, Y750 Tool, UV1L Die Nest, Y34PLA Die Indenter, (1) Crimp, Die Index: 42, Conductor Type: Commercial/Military Stranded Copper, Tongue Angle: Straight, Wire Strip Length: 5/8 IN

Product Details

General

Application	For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance
Connector Type	Terminal
Die Index	42
Feature - Barrel Style	- Chamfered - Skived
Feature - Barrel Type	Standard
Material	Copper
Material Composition	- DLP Copper - Tin Plating
Military Specification	MS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025505

Dimensions

Dimension - B Length fraction	5/8 in
-------------------------------	--------

Dimension - B Length inch	0.60 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - D inch	0.89 in
Dimension - Hole Size mm	13 mm
Dimension - Length Overall inch	1.97 in
Dimension - N inch	0.43 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Pad Width inch	0.86 in
Dimension - Strip Length inch	5/8
Dimension - Z inch	0.46 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor - Copper Str Size	1
Conductor - Copper Str Size Range	1
Conductor Type	- CU C Solid-Size - CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	- UL467 - Military Specified (Mil-Spec)
Standards - Industry Standards Met	- UL467 - Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)