



YAE14Z4BOX

by Burndy
Catalog ID: YAE14Z4BOX

Prop 65 Notice

Flanged Fork Terminal, 16-14 AWG, 8-10, 1.08 in L, .36 in W, Nylon Insulated, Multi-Finger Insulation Grip, 600 Volts Max., 105 Deg C Max.

Features: INSULUG Type YAE-Z Is Identical To Type YAE-N And Employs A Flanged Fork Tongue For Faster Installation While Maintaining Security If Supporting Screw Becomes Loose, 300 V Maximum, 105 DEG C Max, Flanged Fork: Permits Rapid, Easy Installation Of The Terminal Under The Screw Head Without Complete Removal Of The Screw, Additionally, It May Not Be Removed With Only A Slight Loosening Of The Screw, Package: Box, Installation Tool: MR8-33T-1, M8ND Tool With One Of The Following Dies: N14HET-15, N10ET-9, N10ET-23, N14HET-25V1, Y10D, Y10-22 Tool, Insulation Diameter (maximum): 0.156 IN, Tape Mounted Catalog Number: YAE14Z4M, Color Code: Blue, Wire Insulation Grip: Yes, Temperature Rating: 105 DEG C Maximum, Finish: Electro-Tin Plated

Product Details

General

Application	Power Connector
Color Code	Blue
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Electro Tin
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	YAE-Z, Flanged
UPC	781810563809
UPC 12 Digit	7818105638099

Dimensions

Cable Insulation Diameter Maximum	0.156 in
Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	27 mm

Dimension - Length Overall inch	1.08 in
Dimension - N inch	0.24 in
Dimension - Pad Width inch	0.36 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z inch	0.33 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	- UL486 - Military Specified (Mil-Spec)
Standards - Industry Standards Met	- UL486 - Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)