

YAV35M6

by Burndy
Catalog ID: YAV35M6

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W, 35mm, M6 stud, Tin - Electro Plated, 10 Index

One hole hylug code conductor standard barrel, Made from electrolytic copper tube and is electro tin plate.



Product Details

General

Application	Metric Conductor with Window Lug
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	10
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	Terminals, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YAV
UPC	781810235799
UPC 12 Digit	7818102357999

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.46 in
Dimension - Bolt Hole Size inch	0.17 in
Dimension - D inch	0.57 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - Inside Diameter inch	0.31 in
Dimension - L Length Overall mm	3 mm
Dimension - Length Overall inch	0.10 in
Dimension - N inch	0.28 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.68 in

Dimension - Strip Length inch	0.67 in
Dimension - Z inch	0.35 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	2
Conductor - Copper Str Size Range	2
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)