

## YCA252N

by Burndy  
Catalog ID: YCA252N

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 5-3/8 IN L.

Features: NEMA standard mounting holes, Made of pure copper, Installed with same die as equivalent full-tension jumper loop and repair sleeves



## Product Details

### General

Application	Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus
Connector Type	Terminal
Die Index	165
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YCA-2N
UPC	781810810385
UPC 12 Digit	7818108103855

### Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.34 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1 5/8
Dimension - Z inch	2.37 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

### Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)