

YCA262NG6W

by Burndy
Catalog ID: YCA262NG6W

Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Hot tin plated



Product Details

General

Connector Type	Terminal
Die Index	K-5/8-1
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810088722
UPC 12 Digit	7818100887222

Dimensions

Dimension - B Length fraction	1-18/25 in
Dimension - B Length inch	1.72 in
Dimension - D inch	3.03 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.45 in
Dimension - L Length Overall mm	135 mm
Dimension - Length Overall inch	5.30 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Pad Width inch	0.97 in
Dimension - Strip Length inch	1 13/16
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)