

YC2A2

by Burndy
Catalog ID: YC2A2

Prop 65 Notice

Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, 1-1/2" L,Run(Aluminum):2 Sol. & Str.

Features: Range-Taking, C-Shaped Aluminum Compression Tap, Or Dead-Ending Connector Designed To Eliminate Effects Of Cold Flow, Can Be Gripped In Tool And Slipped Over Line For Easy Crimping, Pre-Filled With PENETROX Joint Compound And Stripsealed, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-C Die, (4), Y35, Y750 Tool, U-C Die (2), Y45 Tool, U-C Die With PT-6515 Adapter, (2), Y46 Tool, U-C Die With PUADP-1 Adapter, (2), Die Index: C Element A, Compressed / Compact: No, Conductor Size (run - Range): 2 AWG Solid - 2 AWG Stranded, Conductor Type: Run: Aluminum, Tap: Aluminum, Conductor Size (tap Range): 4 AWG Solid - 4 AWG Stranded, Shape: C



Product Details

General

Application	For Combinations Of Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors
Construction Material - Main	Aluminum
Die Index	C
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-A
UPC	781810121504
UPC 12 Digit	7818101215044

Dimensions

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in

Conductor Related

Conductor - AAAC 5005 Run	48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Tap	48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Tap Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Run	48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Tap	48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Tap Range	48.69 (7) kcmil-77.47 (7) kcmil

Conductor - ACSR Cmpt Run	4 AWG;3 AWG;2 AWG
Conductor - ACSR Cmpt Run Range	4 AWG-2 AWG
Conductor - ACSR Cmpt Tap	4 AWG;3 AWG;2 AWG
Conductor - ACSR Cmpt Tap Range	4 AWG-2 AWG
Conductor - ACSR Str Run Range	4 AWG - 2 AWG
Conductor - ACSR Str Tap Range	4 AWG - 2 AWG
Conductor - AL Str Run	2 AWG
Conductor - AL Str Run Range	2 Sol. - 2 Str
Conductor - AL Str Tap	2 AWG
Conductor - AL Str Tap Range	2 Sol. - 2 Str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)