

YCAB344N

by Burndy
Catalog ID: YCAB344N

Prop 65 Notice

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, Pad width: 2-3/8 IN.

Features: Compression HYLUG Terminals Designed For Terminating Copper Conductors To Switch Pads And Other Substation Or Switch Yard Apparatus, NEMA Standard Mounting Holes, Made Of Pure Copper, Installed With Same Die As Equivalent Full Tension Jumper Loop And Repair Sleeves, Have Brazed Pads, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U210 Die, (6), Y45 Tool, U210 Die With PT-6515 Adapter, (6), Y46 Tool, U210 Die With PUADP-1 Adapter, (6), Y48B Tool, C210 Die, (2), Y60BHU Tool, L210 Die, (2), Die Index: 210



Product Details

General

Application	For Terminating Copper Conductors To Switch Pads And Other Substation Or Switch Yard Apparatus
Connector Type	Terminal
Die Index	210
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YCAB-4N
UPC	781810014851

Dimensions

Dimension - B Length fraction	2-9/17 in
Dimension - B Length inch	2.53 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.81 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.38 in

Dimension - Pad Width inch	3.00 in
Dimension - Strip Length inch	2 5/8
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.63 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)