

YCA282N

by Burndy
Catalog ID: YCA282N

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, Die Index: 168.

Features: NEMA standard mounting holes, Made of pure copper, Installed with same die as equivalent full-tension jumper loop and repair sleeves



Product Details

General

Application	Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus
Connector Type	Terminal
Die Index	168
Material	Copper
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YCA-2N
UPC	781810014783

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.35 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Pad Width inch	1.22 in
Dimension - Strip Length inch	1 11/16
Dimension - Stud Size inch	33/64
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	4/0 AWG
-----------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us**BURNDY Headquarters**

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)