



YCAB444N

by Burndy Catalog ID: YCAB444N

Prop 65 Notice

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus.

Product Details

General

Connector Type	Terminal
Die Index	345
Material	Copper Alloy
Physical Attribute - Number of Crimps Required	4
Physical Attribute - Number of Holes	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810014875

Dimensions

Dimension - B Length fraction	3-9/29 in
Dimension - B Length inch	3.31 in
Dimension - D inch	3 in
Dimension - E Spacing between Holes fraction	1.75 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	198 mm
Dimension - Length Overall inch	7.80 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	2 in
Dimension - Pad Width inch	3 in
Dimension - Strip Length inch	3 3/8
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.63 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	1000 kcmil
Conductor - Copper Str Size Range	1000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109 **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)