

# YCA292N

by Burndy  
Catalog ID: YCA292N



Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 5-5/8 IN L.

Features: NEMA standard mounting holes, Made of pure copper, Installed with same die as equivalent full-tension jumper loop and repair sleeves

## Product Details

### General

Application	Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus
Connector Type	Terminal
Die Index	169
Material	Copper
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YCA-2N
UPC	781810014790

### Dimensions

Dimension - B Length fraction	1- 81/100 in
Dimension - B Length inch	1.81 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.52 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.28 in
Dimension - Strip Length inch	1 7/8
Dimension - Stud Size inch	33/64
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)