



YCAK31AG1

by Burndy
Catalog ID: YCAK31AG1

Prop 65 Notice

Cast Aluminum Alloy Terminal, 2 Pad Holes, 350 kcmil Cu,Al Conc.&
Compact, 317, 705 Index

Product Details

General

Die Index	317;705
Material	Aluminum Alloy, Cast
Physical Attribute - Pad Configuration	1 Hole
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810224
UPC 12 Digit	7818108102244

Dimensions

Dimension - B Length inch	1.94 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - D inch	1.31 in
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.52 in
Dimension - Pad Width inch	1.25 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)