


YCS26R

by Burndy
Catalog ID: YCS26R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 7 IN L.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeves, Pre-Filled With PENETROX Joint Compound, Die Index: 245 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W245 Die, (6), Y35, Y750 Tool, U245 Die, (3), Y45 Tool, U245 Die With PT-6515 Adapter, (3), Y46 Tool, U245 Die With PUADP-1 Adapter, (3), Conductor Type: ACSR, 6201, 5005, Aluminum



Product Details

General

Application	For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors
Connector Type	Splice
Die Index	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810820797
UPC 12 Digit	7818108207977

Dimensions

Dimension - B Length inch	3.55 in
Dimension - L Length Overall mm	179 mm
Dimension - Length Overall inch	7.05 in
Dimension - Outside Diameter inch	0.70 in

Conductor Related

Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 (7, 19) AWG
Conductor - AL Str Size Range	2/0 (7, 19) AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)