

YCS351A

by Burndy
Catalog ID: YCS351A

Prop 65 Notice

Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION),Die Index: 261.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeve, Pre-Filled With PENETROX Joint Compound And Capped, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U261 Die, (6), Y45 Tool, U261 Die With PT-6515 Adapter, (6), Y46 Tool, U261 Die With PUADP-1 Adapter, (6), Y48B Tool, C261 Die, (2), Y60BHU Tool, L261 Die, (2), Die Index: 261 Element A, Conductor Type: Compressed Aluminum, Compact Aluminum, Commercial Aluminum



Product Details

General

Application	For All Aluminum, Compressed And Compact Conductors
Connector Type	Splice
Die Index	261
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-A
UPC	781810015148
UPC 12 Digit	7818100151488

Dimensions

Dimension - B Length inch	4.31 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in
Dimension - Outside Diameter inch	1.39 in

Conductor Related

Conductor - AL Str Size	556.5 kcmil
-------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)