

YCR27RG5

by Burndy
Catalog ID: YCR27RG5

HYSPLICE™ REDUCER(CU-ACSR)



Product Details

General

Color Code	Purple
Connector Type	Reducer
Die Index	654;705
Material	Aluminum
Oxide Inhibitor Type	Penetrox A
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810324578

Dimensions

Dimension - A Outside Diameter inch	1.06 in
Dimension - B Length fraction	2-22/25 in
Dimension - B Length inch	2.88 in
Dimension - B Outside Diameter inch	1.06 in
Dimension - L Length Overall mm	162 mm
Dimension - Length Overall inch	6.38 in
Dimension - Strip Length inch	3

Conductor Related

Conductor - AAAC 5005 Size A	195.7 (7) kcmil
Conductor - AAAC 5005 Size A Range	195.7 (7) kcmil
Conductor - AAAC 5005 Size B	123.3 (7) kcmil
Conductor - AAAC 5005 Size B Range	123.3 (7) kcmil
Conductor - AAAC 6201 Size A	195.7 (7) kcmil
Conductor - AAAC 6201 Size A Range	195.7 (7) kcmil
Conductor - AAAC 6201 Size B	123.3 (7) kcmil
Conductor - AAAC 6201 Size B Range	195.7 (7) kcmil
Conductor - ACSR Cmp Size A	3/0 (6/1) Pigeon
Conductor - ACSR Str Size A	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size A Range	3/0 (6/1) Pigeon AWG

Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	3/0 AWG
Conductor - AL Str Size A Range	3/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - AL Str Size B Range	1/0 AWG
Conductor - Copper Str Size A	3/0 AWG
Conductor - Copper Str Size A Range	3/0 AWG
Conductor - Copper Str Size B	1/0
Conductor - Copper Str Size B Range	1/0

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)