

YCS26

by Burndy
Catalog ID: YCS26

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Die index:166.

Features: Loop HYSPLICE Connector Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Pure Copper Tubing, Installed With Standard HYSPLICE Tools And Dies, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W166 Die, (6), Y750, Y35 Tool, U166 Die, (3), Y45 Tool, U166 Die With PT-6515 Adapter, (3), Y46 Tool, U166 Die With PUADP-1 Adapter, (3), Die Index: 166 Element A, Conductor Type: Copper



Product Details

General

Application	For Copper Conductors
Connector Type	Splice
Die Index	166
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS
UPC	781810014189
UPC 12 Digit	7818100141899

Dimensions

Dimension - A Outside Diameter inch	0.71 in
Dimension - B Length fraction	1-36/61 in
Dimension - B Length inch	1.59 in
Dimension - B Outside Diameter inch	0.71 in
Dimension - L Length Overall mm	85 mm
Dimension - Length Overall inch	3.34 in

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)