

YCS45R

by Burndy
Catalog ID: YCS45R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index:352.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeves, Pre-Filled With PENETROX Joint Compound, Tools, Die Set Catalog Number, And (number Of Crimps): Y45 Tool, S352 Die, (9), Y46 Tool, P352 Die, (9), Y48B Tool, C352 Die, (3), Y60BHU Tool, L352 Die, (3), Die Index: 352 Element A, Conductor Type: ACSR, 6201, 5005, Aluminum

Product Details

General

Application	For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors
Connector Type	Splice
Die Index	352
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810015094
UPC 12 Digit	7818100150944

Dimensions

Dimension - B Length fraction	5-1/4 in
Dimension - B Length inch	5.25 in
Dimension - L Length Overall mm	270 mm
Dimension - Length Overall inch	10.62 in

Conductor Related

Conductor - AAAC 5005 Size	927.2 (37)
Conductor - AAAC 5005 Size Range	927.2 (37)
Conductor - AAAC 6201 Size	927.2 (37)
Conductor - AAAC 6201 Size Range	927.2 (37)
Conductor - ACSR Str Size	795 (26/7) Drake
Conductor - ACSR Str Size Range	795 (26/7) Drake
Conductor - AL Str Size	795.5
Conductor - AL Str Size Range	795.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)