

# YDS6C

by Burndy  
Catalog ID: YDS6C

Prop 65 Notice

CU Full tension splice, ANSI C119.4 Class 1A(Normal Tension),2-3/4 IN L.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W161 Die, (2), Y35, Y750 Tool, U161 Die, (1), Y45 Tool, U161 Die With PT-6515 Adapter, (1), Y46 Tool, U161 Die With PUADP-1 Adapter, (1), Die Index: 161 Element A, Conductor Type: Stranded Copper



## Product Details

### General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	161
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS - C
UPC	781810821077

### Dimensions

Dimension - B Length fraction	1-13/50 in
Dimension - B Length inch	1.26 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.77 in
Dimension - Outside Diameter inch	0.32 in

### Conductor Related

Conductor - Copper Str Size	6 AWG
-----------------------------	-------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

**Logistics**

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)