



## YDS1C

by Burndy  
Catalog ID: YDS1C

Prop 65 Notice

CU Full tension splice, Index: 164.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 164 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W164 Die, (6), Y35, Y750 Tool, U164 Die, (3), Y45 Tool, U164 Die With PT-6515 Adapter, (3), Y46 Tool, U164 Die With PUADP-1 Adapter, (3), Conductor Type: Stranded Copper

## Product Details

### General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	164
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS - C
UPC	781810564868

### Dimensions

Dimension - B Length inch	2.05 in
Dimension - L Length Overall mm	109 mm
Dimension - Length Overall inch	4.29 in
Dimension - Outside Diameter inch	0.56 in

### Conductor Related

Conductor - Copper Str Size	1 AWG
-----------------------------	-------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)