


## YDS6W

by Burndy  
Catalog ID: YDS6W

Prop 65 Notice

CU Full tension splice, ANSI C119.4 Class 1A(Normal Tension),2-5/8 IN L.

Features: YDS-W Is Designed To Develop Full Rated Breaking Strength Of Hard Drawn And Medium Hard Drawn Solid Copper Conductor, Made Of Pure Copper Tubing, Installed With Standard Tooling, Die Index: 161 Element A, Conductor Type: Solid Copper, Tools, Die Set Catalog Number, And (number Of Crimps): MD7, MD6 Tool, W161 Die, (2), Y35, Y750 Tool, U161 Die, (1), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1



## Product Details

### General

Application	For Solid Copper Conductors
Connector Type	Splice
Die Index	161
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810820667

### Dimensions

Dimension - B Length inch	1.27 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Outside Diameter inch	0.32 in

### Conductor Related

Conductor - Copper Solid Size	6 AWG
-------------------------------	-------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)