


YDS2W

by Burndy
Catalog ID: YDS2W

Prop 65 Notice

CU Full tension splice.

Features: YDS-W Is Designed To Develop Full Rated Breaking Strength Of Hard Drawn And Medium Hard Drawn Solid Copper Conductor, Made Of Pure Copper Tubing, Installed With Standard Tooling, Die Index: 163 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W163 Die, (6), Y35, Y750 Tool, U163 Die, (2), Y45 Tool, U163 Die With PT-6515 Adapter, (2), Y46 Tool, U163 Die With PUADP-1 Adapter, (2), Conductor Type: Solid Copper



Product Details

General

Application	For Solid Copper Conductors
Connector Type	Splice
Die Index	163
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-W
UPC	781810868270

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - Outside Diameter inch	0.48 in

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Size	3 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)