


YDS75

by Burndy
Catalog ID: YDS75

Prop 65 Notice

Copper splice designed to develop full rated breaking strength of hard drawn and medium hard drawn solid copper conductor. ANSI C119.4 Class 1 (Full Tension), Die index:165.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 165 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W165 Die, (6), Y35, Y750 Tool, U165/U205 Die, (6), Y45 Tool, U165/U205 Die With PT-6515 Adapter, (6), Y46 Tool, U165/U205 Die With PUADP-1 Adapter, (6), Conductor Type: Solid Copper



Product Details

General

| | |
|--|-----------------------------|
| Application | For Solid Copper Conductors |
| Connector Type | Splice |
| Die Index | 165;287 |
| Material | Copper |
| Oxide Inhibitor Type | Penetrox E |
| Physical Attribute - Number of Crimps Required | 6 |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | HYSPLICE |
| Trade Name | HYSPLICE™ |
| Type | YDS |
| UPC | 781810564806 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length inch | 2.84 in |
| Dimension - L Length Overall mm | 151 mm |
| Dimension - Length Overall inch | 5.93 in |
| Dimension - Outside Diameter inch | 0.61 in |

Conductor Related

| | |
|-------------------------------|---------|
| Conductor - Copper Solid Size | 1/0 AWG |
|-------------------------------|---------|

Certifications and Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)