

YE31P46X92FX

by Burndy
Catalog ID: YE31P46X92FX

Prop 65 Notice

Copper Adaptor Plugs, 262.6 (650/#24) DLO, 250 Flex Class I,K,M, 17 Index, Cable Strip Length: 2-1/2 IN



Product Details

General

Color Code	White
Connector Type	Pin Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Insulation	Y
Material	Copper
Pin Type	Straight
Plated	Yes
Plating Type	Tin plated
Type	Copper Pin Adapters
UPC	781810037874
UPC 12 Digit	7818100378744

Dimensions

Dimension - A Outside Diameter inch	0.51 in
Dimension - B Length fraction	2-3/8 in
Dimension - B Length inch	2.53 in
Dimension - B Outside Diameter inch	0.95 in
Dimension - Inside Diameter inch	0.7 in
Dimension - L Length Overall mm	94 mm
Dimension - Length Overall inch	4.00 in
Dimension - Outside Diameter inch	0.88 in
Dimension - P inch	1.02 in
Dimension - Strip Length inch	2.63 in
Equivalent Cross Pin Size	0.46 in. - 4/0 AWG
Equivalent Pin Size	4/0 AWG

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	313 DLO
Conductor - Copper DLO Size Range	262.6 (650/#24) DLO
Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex I Size Range	250 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex K Size Range	250 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Flex M Size Range	250 kcmil
Conductor - Copper Str Size	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)