

YF1010UI

by Burndy
Catalog ID: YF1010UI

Prop 65 Notice

Cu Alloy Bare Ferrule, Smooth Funnel Entry, 10 AWG, 0.39" L, Seamless bbl, Tin Plated, For Use On Cu Cond.

Features: Wire Ferrules Are Also Known As Cord End Terminals Or Bootlace Ferrules, These Are Electrical Connectors Used To Terminate Stranded Wires, These Terminals Are Made Of Electrolytically Tin Plated Copper, Uninsulated Ferrules Are Designed To Form Neat End Terminations To Multi-Strand Cables Or Wires, Smooth Funnel Entry Assists In Wire Insertion, Specifically Designed To Aid In Termination Of Extra Flexible Fine Stranded Conductor, Provides Enhanced Flexibility Relating To Wire Termination And Management, A Positive Contact Surface Helps Ensure System Integrity, Made Of Electrolytic Copper, Tin Plated, Seamless Barrels, Smooth Funnel Entry To Make Wire Insertion Easier, RoHS Compliant, Recommended Tooling: YF3206TOOL, YF2610TOOL, YF2210TOOL, YF1006TOOL



Product Details

General

| | |
|--------------|-----------------------------|
| Application | For Use On Copper Conductor |
| Material | Copper |
| Sub Brand | FERRULES |
| Type | Bootlace Ferrule |
| UPC | 781810479582 |
| UPC 12 Digit | 7818104795822 |

Dimensions

| | |
|--------------------------------|----------|
| Dimension - D inch | 0.15 in |
| Dimension - D1 inch | 0.14 in |
| Dimension - D2 inch | 0.21 in |
| Dimension - Length Side A inch | 0.39 in |
| Length | 0.388 in |
| Width | 0.205 in |

Conductor Related

| | |
|-------------------------------|--|
| Conductor - Copper Solid Size | 10 AWG |
| Conductor - Copper Str Size | 10 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

| | |
|-----------------------|--------|
| Carton Quantity | 250 EA |
| Minimum Pack Quantity | 250 |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)