



YGF342N

by Burndy
Catalog ID: YGF342N

Prop 65 Notice

Cast Copper Alloy Grounding Plate, 2 Pad Holes, 250 kcmil-500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Standard Thread.

Product Details

General

Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYGROUND®
UPC	781810002131
UPC 12 Digit	7818100021311

Dimensions

Dimension - D inch	3.25 in
Dimension - Height fraction	4-31/50 in
Dimension - Height inch	4.62 in
Dimension - L Length Overall mm	137 mm
Dimension - Length Overall inch	5.40 in
Dimension - Pad Width inch	2.00 in
Dimension - Thread Size	3/8 -16
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	NEMA Size Holes
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• IEEE 837
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)