

YNA32RT15H

by Burndy
Catalog ID: YNA32RT15H

Prop 65 Notice

HYLUG™, Aluminum Tube Compression Terminal operates at 345 Kv, 300-336.4 Kcmil ACSR, 336.4-350 Kcmil Al, 395.1-395.5 Kcmil ACAR, Cable to flat, Terminal available with H/W, 15 Deg



Product Details

General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Number of Holes	2
Trade Name	HYLUG™
UPC	781810514849
UPC 12 Digit	7818105148499

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	230 mm
Dimension - Length Overall inch	9.04 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in
Dimension - Width fraction	1.68 in
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACAR Str Size	395.1;395.2
Conductor - ACAR Str Size Range	395.1;395.2
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350
Conductor - AL Str Size Range	336.4;350

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)