

YNA7M7T

by Burndy
Catalog ID: YNA7M7T

Prop 65 Notice

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #7 Alumoweld, 7/16 Steel, 7 Str.



Product Details

General

Connector Type	Terminal
Die Index	678;726
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810180525
UPC 12 Digit	7818101805255

Dimensions

Dimension - B Length inch	4.19 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	253 mm
Dimension - Length Overall inch	9.95 in
Dimension - Outside Diameter inch	1.00 in
Dimension - Pad Width inch	1.5 in

Conductor Related

Conductor - Galvanized Steel Str Size	7/16 (7) in
Conductor - Galvanized Steel Str Size Range	7/16 (7) in
Conductor Type	GAL Steel C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)